

Room partitioning – easy and quick

with the telescopic drywall support ST



Tool and material recommendations:

- Telescopic drywall support ST250 / ST290 (one support every 2 metres)
- Foil as a release material (e.g. B1, flame retardant)
- Multi-purpose shears D820 for cutting the foil
- Spring clamps Clippix XC2 / XC3 and sticky tape to attach the foil to the drywall support



1

Cut the foil to the required size. Note a foil overhang of approx. 10 cm per side.



2

Fix the foil with the help of an adhesive tape on the upper support surface of the drywall support.



3

Now press the release button and pull the telescopic rod out until the support surface and the ceiling touch. Then pull the lower part of the foil under the support surface of drywall support on the floor.



4

As soon as the drywall support stands vertically between the ceiling and the floor, turn the handle clockwise to fix the support firmly.



5

Finally, the protruding foil must be attached to the drywall supports. To do this, use adhesive tape or, as shown in the picture, spring clamps that can be fixed quickly.



Note:
It is recommended above for dust protection walls and wooden slats below to attach.

Room partitioning – easy and quick

These BESSEY products will help you!




- Resilient up to a maximum of 150 kg when the telescopic rod is fully retracted
- Stable construction due to special steel pipes and anti-slip PVC contact surfaces
- Application also on slopes due to continuously swivelable contact surfaces of -45° to +45°
- Easy, safe handling due to a telescoping and locking inner pipe as well as an outer pipe that can be turned by the foam grip
- GS-certified for quality and safety



Telescopic drywall support ST

Order-No.	Adjusting range mm	Load limit		kg	qty.	V3
		at min. extension length kg	at max. extension length kg			
ST250	1450-2500	150	60	2.06	2	
ST290	1600-2900	150	50	2.24	2	

- Lightweight, functional and easy to handle
- Extremely sturdy



Spring clamp Clippix XC

Order-No.	Opening		Throat depth		kg	qty.	V3
	mm	"	mm	"			
XC2	25	1	30	1 1/8	0.02	10	
XC3	35	1 3/8	37	1 1/2	0.05	10	

- Stainless steel blades
- Comfortable handles loops with soft cushion inserts



Multi-purpose shears D820

Order-No.	Overall length		Blade length		kg	qty.	V5
	mm	"	mm	"			
D820-200	200	7 7/8	80	3 1/3	0.07	12	
D820-250	250	10	105	4 1/4	0.10	12	

More information
www.bessey.de



Your dealer: